

Datasheet – TEC Controller TEC-1163 (±25 A / ±56 V)



Support / First steps

Meerstetter Engineering provides technical support for all products and helps you to integrate a product into your solution. Most of your questions should be solved by reading the provided <u>user manuals</u> of the corresponding product or the <u>FAQ</u> (frequently asked questions).

For further help or if you have any other questions, please do not hesitate to contact us. We are happy to help you. You can contact us by email <u>support@meerstetter.ch</u>.

Meerstetter's product family compatibility

The Meerstetter LDD and TEC-Family have been developed to work along with each other. They share the same platform bus, communication protocol and hardware architecture. See Table for an Overview over the LDD- and TEC-Families.

LDD-Family		
LDD-1321	0-1.5 A / 0-14 V	CW, Add on TEC Controller available
LDD-1301	0-20 A / 0.5-45 V	1 ms - CW
LDD-1303	0-20 A / 1-120 V	1 ms - CW
LDD-1137	0-75 A / 0-70 V	0.5 μs - CW, modulated, QCW and pulsed modes
LDD-1124-SV	0-1.5 A / 0-15 V	1 μs - CW, modulated, QCW and pulsed modes
LDD-1121-SV	0-15 A / 0-15 V	1 μs - CW, modulated, QCW and pulsed modes
LDD-1125-HV	0-30 A / 0-27 V	1 μs - CW, modulated, QCW and pulsed modes
TEC-Family		
TEC-1092	±1.2 A / ±9.6 V	Micro, single channel
TEC-1091	±4 A / ±21 V	Small, single channel
TEC-1089-SV	±10 A / ±21 V	Medium, single channel
TEC-1162	±5 A / ±56 V	Medium-high, single channel
TEC-1090-HV	±16 A / ±30 V	Large, single channel
TEC-1163	±25 A / ±56 V	Extra-large, single channel
TEC-1161-4A	2 x (±4 A / ±21 V)	Small, dual channel
TEC-1161-10A	2 x (±10 A / ±21 V)	Medium, dual channel
TEC-1122-SV	2 x (±10 A / ±21 V)	Medium, dual channel
TEC-1166	2 x (±5 A / ±56 V)	Medium-high, dual channel
TEC-1123-HV	2 x (±16 A / ±30 V)	Large, dual channel
TEC-1167	2 x (±25 A / ±56 V)	Extra-large, dual channel

One Channel OEM TEC Controller



Description:

The TEC-1163 is a specialized TEC Controller/power supply able to precision-drive one Peltier element.

• It features a true bipolar DC current source for cooling / heating, three temperature monitoring inputs (1x high resolution, 2x low resolution) and intelligent PID control with auto tuning. The TEC-1163 is fully digitally controlled, it's hard-and firmware offer numerous communication and safety options.

• The included PC-Software allows configuration, control, monitoring and live diagnosis of the TEC Controller via USB, RS232 TTL and RS485. All parameters are saved to non-volatile memory. Saving can be disabled for bus operation.

• For the most straightforward applications, only a power supply, a Peltier element and at least one temperature sensor need to be connected to the TEC-1163. After power-up the unit will operate according to pre-configured values. (In stand-alone mode no control interface is needed.)

• The TEC-1163 can handle either Pt100, Pt1000, NTC or Voltage temperature probes. For highest precision and stability applications a Pt100 / 4-wire input configuration is recommended. Analog measurement circuit is factory calibrated.

• Auxiliary temperature inputs allow the connection of NTC probes that are located on the heat sinks of the Peltier elements. This additional data is used to compensate for parasitic thermal conduction of Peltier elements. Also, it allows the control of external heat sink cooling fans. • The heating and cooling power is optimized by proprietary thermal management routines based on power balance models (for Peltier elements and resistive heaters).

• Further functionality includes: Smooth temperature ramping, thermal stability indication and auto gain (NTC probes). The PC-Software allows data logging and configuration import/export.

Features

Input Characteristics:

• DC Input Voltage: 11.5 to 63 V

Output Characteristics:

- Voltage: up to ± 56 V
- Current: up to ± 25 A

Main Features:

- Temperature Sensor Types: Pt100, Pt1000, NTC, Voltage
- Temperature Precision / Stability: < 0.01 °C
- Temperature Control & Measurement Frequency: 1 Hz, 10 Hz, 90 Hz
- Communication bus compatible
- Configuration and monitoring with Service Software

Operation Modes:

- Stand-alone operation
- Remote-controlled over USB, RS485, RS232 TTL, CANopen CiA 301, I/O
- Script-controlled over lookup table (thermal cycling)

Driver Modes:

- DC power supply (bipolar)
- Temperature control: PID settings, auto tuning, optional cool/heat-only or resistor heating modes

Important Note:

The following features will be activated with an incoming firmware update, but are not yet useable:

- GPIO9 and GPIO10
- Low-resolution temp. measurement input 3




General Characteristics


Absolute	Maximum	Ratings
mosolute	Maximum	natings

Supply voltage (DC)	70V

Operating Ratings	
Temperature	-40 – 70°C
Humidity	5 – 95 % non-condensing

Operating Characteristics






Note:

Standard or Extended Device Temperature Mode can be set as software setting. No forced air flow was present.

Efficiency



Note:

The Efficiency measurements were done at 48 V input voltage, an output voltage of 44 V, an output current of 25 A and a base plate temperature of 60°C unless otherwise noted. The ambient temperature was 23°C, no forced air flow was present.



Symbol	Parameter	Test Conditions	Min	Тур	Max	Units
DC Power	Supply Input:					
UIN	Supply voltage		11.5		63	V
UIN Ripple	Ripple tolerance	U_{IN} never below U_{IN} min or above U_{IN} max			300	mVPP
Output:						
Іоит	Bipolar current swing				±25	А
Uout	Bipolar voltage swing	Uout is maximum ~0.90 UIN			±56	v
UOUT Ripple	Voltage ripple	@ 25 A			120	mVPP
System Ch	aracteristics:					
ղ50%	Power efficiency	@ 50% load (28 V, 25 A)		93		%
η 100%	Power efficiency	@ 100% load (56 V, 25 A)		95		%
Output Mo	onitoring (Iour Resol	ution is 18.3 mA; U _{OUT} Resolution is	17.6 mV	/):		
IOUT Read	Precision	@ 24 A		1	5	%
UOUT Read	Precision	@ 30.0 V		1	3	%

Output Safety Characteristics Unless otherwise noted: $T_A = 25$ °C, $U_{IN} = 48$ V

Symbol	Parameter	Test Conditions / Hints	Min	Тур	Max	Units
Output Sta	ge Protection Dela	iys:				
t _{OFF} short circuit		Full load condition		10	30	μs
toff power system limits		Current and voltage limits			200	μs
-	ge Current Superv	ision: nuch, an error is generated)				
Iout diff	Error threshold			2.5		А

High Resolution Temperature Measurement Characteristics (NTC Probes)

NTC thermistor resistive input characteristics translate into temperature ranges valid for only one type of NTC probe. Below example is given in the case of an NTC B25/100 3988K R25 10k temperature sensor.

Symbol	Parameter	Test Conditions	Min	Тур	Max	Units
Dup purer	ADC auto gain		73		1 M	Ω
KHR, RANGE	PGA = 1 or 8 or 32		194.3 to -55.5		°C	

ROBJ, RANGE is resistance range of the NTC sensor.



Measurement configuration = 23 bit / 4-wire / unshielded cable <50 mm

Symbol	Parameter	Test Conditions	Min	Тур	Max	Units
Tobj, range	Range	Range is extendable upon request. Extended measurement range is -193 °C +787 °C	-220		+200	°C
Tobj, prec	Precision	(EN 60751 / IEC 751)		5		mK
Tobj, coeff	Temp. coefficient	Relative to device temperature			1.6	mK/K
Tobj, noise	Value noise	Reference measurement fluctuations while output stage operating @ 70 % load		5		mK
Tobj, rep	Repeatability	Repeated measurements of reference resistors after up to 3 days		8		mK

High Resolution Temperature Measurement Configuration (Voltage Measurement VIN1/2)

Sensors with linear Voltage/Temperature output.

Symbol	Parameter	Test Conditions	Min	Тур	Max	Units
V _{SENS} , diff	Range	Differential input voltage Temperature range depends on sensor used	-2.039		2.039	V
Tobj, range	Range	Absolute input voltage	-0.1		5.1	V

Low Resolution Temperature Measurement Characteristics (NTC only)

T_A = 25 °C, measurement configuration = 12 bit / 2-wire / unshielded cable <50 mm, °T probe = NTC B25/100 3988K R25 10k							
Symbol	Parameter	Test Conditions	Min	Ту	Max	Units	
				р			
Departmen	Dango	Corresponding tomporature range	83		182413	Ω	
Rlr, range	ANGE Range Corresponding temperature range			-30 to 2	187	°C	

General Purpose Digital I/O Characteristics (GPIO1 ... GPIO10)

Symbol	Parameter	Test Conditions	Min	Тур	Max	Units
Input Cha	aracteristics:					
(Microproces				r		
Uih	Logic high input threshold		2.38			V
Uil	Logic low input threshold				0.93	V
UIMAX	Maximum input voltage		-0.5		5.5	V
(Microproces						
Uон	Logic high output voltage	Output current 8 mA	2.8		3.3	V
Uol	Logic low output voltage	Input current 8 mA			0.4	V
Zout	Output impedance			50		Ω
				-		
Iout	Output sink or source current			±8	±20	mA
Iout ESD Prot				±8	±20	mA
ESD Prot				±8	±20	mA
ESD Prot	ection:	IEC61000-4-2		±8 18	±20	mA kV




Auxiliary Connector X8, X9, X10 Power Supply Output Characteristics Unless otherwise noted: T_A = 25 °C

Symbol	Parameter	Test Conditions	Min	Тур	Max	Units		
Input Characteristics:								
Uout	Output voltage	Output current 50mA	4.4	4.5	5	V		
Iout	Output current	Sum of output currents of X8, X9 and X10	0	150	200	mA		
Uimax	Maximum input voltage		-0.5		5.5	V		



PCB-Overview



Connector X1 – X5

Parameter	Min	Тур	Max	Units
Matching screw		M4x6		
Tightening torque		2.2		Nm

Connector X8, X9, X14 TB (Terminal Block) version

Matching Receptacle: Würth WR-TBL Series 382. Würth Part Number 691381000008. Pin 1 is marked in red.

Parameter	Min	Тур	Max	Units
Wire thickness	0.2		1.5	mm ²

For pinout description: see next paragraph.

Connector X8, X9, X14 CON version

Matching Receptacle: Molex Nano-Fit. Molex Part Number 1053071208. Pin 1 is marked in red.

Pinout Com Connector X8 (TB and CON version)			
PIN 1	+5V	PIN 5	RS232 TTL TX
PIN 2	GND	PIN 6	RS232 TTL RX
PIN 3	RS485 1 A/D+	PIN 7	CAN1 H
PIN 4	RS485 1 B/D-	PIN 8	CAN1 L

Pinout GPIO Connector X9 (TB and CON version)				
PIN 1	+5V	PIN 5	GPIO 3	
PIN 2	GND	PIN 6	GPIO 4	
PIN 3	GPIO 1	PIN 7	GPIO 5	
PIN 4	GPIO 2	PIN 8	GPIO 6	

Pinout Temp Measurement Connector X14 (TB and CON version)			
PIN 1	HR Temp IA	PIN 5	LR Temp 1 A
PIN 2	HR Temp IB	PIN 6	LR Temp 1 B
PIN 3	HR Temp UA	PIN 7	LR Temp 3 A

TEC Controller / Peltier Driver up to ±25 A / up to ±56 V

PIN 8

Sea Member of Berndorf Group

meerstetter

PIN 4 HR Temp UB

LR Temp 3 B

Connector X10, X11

Matching Receptacle: Würth Mini Module. Würth Part Number 690157000472. Pin 1 is marked in red.

Pinout Aux Com Connector X10				
PIN 1	+5V	PIN 3	CAN2 H (CAN2 is not available)	
PIN 2	GND	PIN 4	CAN2 L (CAN2 is not available)	

Pinout Aux GPIO Connector X11			
PIN 1	GPIO 7	PIN 3	GPIO 9
PIN 2	GPIO 8	PIN 4	GPIO 10

Connector Specifications X12

The Mini USB Connector X12 can be used to communicate with the TEC Controller using the meCom communications protocol or the Service Software. It is electrically isolated.

Connector Specifications X13

The Connector X13 can be used to connect one of the OLED Displays available from Meerstetter (DPY-1113, DPY-1114 or DPY-1115)


Temperature Measurement Configuration

The Jumpers "2W/4W" are used for the 2 Wire / 4 Wire configuration. For the values of RS and RP please refer to the TEC Controller User Manual.

Mounting Holes M1 - M7

All Mounting holes have a Diameter of 3.05mm. Holes M5-M7 (Marked in red) are used to mount the aluminum base plate to the device and should not be removed.


Temperature Sensor Connection X14





Dimensions and Mounting Hole Positions

Top View, all measurements in mm.





Operation-Modes / Theor	y of Operation	
•	sion TEC Controller that is available with Te sually indicated by on-board green and red L	
CON locking Connector equipped (Best suited for series production)	(Best suited for protot	equipped version yping, commissioning and small series. rts for Terminal Blocks will not be shipped
CANopen or by USB. The TEC-	ed at any time by industry standard connect 1163 can also operate in a remotely controll croller has Scripting capability by sequential	ed manner, with parameters ad-
trol case, temperature data ma Configurable parameters furth (NTC), temperature acquisitio nominal temperature ramping	ply, the TEC-1163 can handle current and vo by be passed on to be processed by the host. Her include sensor linearization (Pt100 / Pt1 In hardware calibration, Peltier element mod C, current, voltage and temperature limits, er al (Document 5216) for further information.	000) and Steinhart-Hart modeling eling, PID controller auto tuning, ror thresholds, etc. Please refer to
Example Configuration: TEC-11 TEC Model: -TEC-1163 High R - PT100	esolution Sensor Type:) (4 Wire)) (4 Wire) 2 Wire) 2 Wire)	Customer Specific Hardware: - Indicates a Customer Specific Hardware Configuration Normally left blank
High Resolution SensorType: Thermocouple:To use our TEC Controller with a VIN1 Object SensorType configurat	with thermocouplestype K, you need \overline{a} CI-1181 in addition to ion.	theTEC Controller
Meerstetter Engineering GmbH Schulhausgasse 12 3113 Rubigen, Switzerland	Member of Berndorf Group	+41 31 529 21 00 contact@meerstetter.ch www.meerstetter.ch
mation furnished by ME is believed to	reserves the right to make changes without further noti be accurate and reliable. However typical parameters on the All operating parameters must be validated by the cu	can vary depending on the application and



Thermoelectric Cooling Temperature Controller TEC Controller / Peltier Driver up to ±25 A / up to ±56 V



Annex A.	Change history		
Date of change	Doc/V	Changed/	Change / Reason
	ersion	Approved	
6 July 2023	А	HS / ML	Document Created
13 December 2023	В	LS / MR	Add front page